

## PaperOne Offset Typical Properties

| Properties           | Unit   | Testing<br>method | Tolerance | Grammage |       |       |       |       |       |       |       |       |        |        |
|----------------------|--------|-------------------|-----------|----------|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|
|                      |        |                   |           | 55       | 60    | 70    | 75    | 80    | 90    | 100   | 120   | 140   | 150    | 160    |
| Grammage             | gsm    | ISO 536           | ± 3%      | 55       | 60    | 70    | 75    | 80    | 90    | 100   | 120   | 140   | 150    | 160    |
| Grammage             | Ibs    | TAPPI 410         | ±3        | 37.40    | 40.80 | 47.60 | 51.00 | 54.40 | 61.20 | 68.00 | 81.60 | 95.20 | 102.00 | 108.80 |
| Thickness            | μm     | ISO 534           | ±3        | 67       | 76    | 86    | 93    | 98    | 110   | 120   | 142   | 161   | 170    | 178    |
| Caliper              | mils   | TAPPI 411         | ± 0.11    | 2.64     | 2.99  | 3.39  | 3.66  | 3.86  | 4.33  | 4.72  | 5.59  | 6.34  | 6.69   | 7.01   |
| Moisture             | %      | ISO 287           | ± 0.5     | 6.0      | 6.0   | 6.0   | 6.0   | 6.0   | 6.0   | 6.0   | 6.0   | 5.5   | 5.5    | 5.5    |
| CIE Whiteness        |        | ISO 11475         | ± 2       | 158      | 158   | 158   | 158   | 158   | 158   | 158   | 158   | 158   | 158    | 158    |
| ISO Brightness       | %      | ISO 2470          | ±2        | 95       | 95    | 95    | 95    | 95    | 95    | 95    | 95    | 95    | 95     | 95     |
| GE Brightness        | %      | TAPPI 452         | ±2        | 93       | 93    | 93    | 93    | 93    | 93    | 93    | 93    | 93    | 93     | 93     |
| ISO Opacity          | %      | ISO 2471          | ±2        | 84       | 88    | 92    | 93    | 94    | 94    | 96    | 97    | 97    | 97     | 98     |
| Roughness            | ml/min | ISO 8791-2        | ±50       | 150      | 150   | 150   | 150   | 150   | 150   | 150   | 150   | 190   | 190    | 190    |
| Shieffeld Smoothness | su     | TAPPI 555         | ±50       | 120      | 120   | 120   | 120   | 120   | 120   | 120   | 120   | 140   | 140    | 140    |

Pangkalan Kerinci, April 30th 2020

Distributed/distribué by



multiplex.solutions